

# CUI

## Anatomical Breast Implants

- Full and Moderate Height Options

- Cohesive Gel


- MicroCell™ Textured Surface Designed to Reduce Capsular Contracture

- DRIE™ Barrier Shell Technology for Reduced Silicone Diffusion



### CMM

**Cohesive Gel**  
**Moderate Projection**




#### CMM - Moderate Height (9 sizes)

Catalogue Number	Product Size (g)	Width A (cm)	Height B (cm)	Projection C (cm)
CMM-160	160	10.0	9.1	3.6
CMM-185	185	10.5	9.6	3.8
CMM-215	215	11.0	10.1	4.0
CMM-245	245	11.5	10.6	4.2
CMM-280	280	12.0	11.1	4.4
CMM-320	320	12.5	11.6	4.6
CMM-360	360	13.0	12.1	4.8
CMM-400	400	13.5	12.5	5.0
CMM-450	450	14.0	12.9	5.2

### CFM

**Cohesive Gel**  
**Moderate Projection**




#### CFM - Full Height (10 sizes)

Catalogue Number	Product Size (g)	Width A (cm)	Height B (cm)	Projection C (cm)
CFM-155	155	9.5	10.0	3.4
CFM-180	180	10.0	10.5	3.6
CFM-205	205	10.5	11.0	3.8
CFM-235	235	11.0	11.5	4.0
CFM-270	270	11.5	12.0	4.2
CFM-310	310	12.0	12.5	4.4
CFM-350	350	12.5	13.0	4.6
CFM-395	395	13.0	13.5	4.8
CFM-440	440	13.5	14.0	5.0
CFM-500	500	14.0	14.5	5.2

# CUI

## Breast Implants



Nominal dimensions: device dimensions are measured with the device placed on a flat surface. Not every device will conform to the dimensions given, slight variations may occur.

## Customer Service

Kronans Droghandel: +46 (0)771 462633

TM marks owned  
by Allergan Inc



Date of preparation: March 2009

ND/0017/2009

Allergan Norden AB, Johanneslundsvägen 3-5  
S-194 81 UPPLANDS VÄSBY

©Allergan Inc 2009





# Round Breast Implants

- Low and High Projection Choices


- Responsive and Cohesive Gel Options



- MicroCell™ Textured Surface Option Designed to Reduce Capsular Contracture

- DRIE™ Barrier Shell Technology for Reduced Silicone Diffusion

**MLP/MHP**  
**Responsive Gel**  
**Textured Surface**




## MLP - Low Profile (13 sizes)

Catalogue Number	Product Size (g)	Diameter A (cm)	Projection B (cm)
MLP-110	MLP-110	8.7	3.0
MLP-140	MLP-140	9.0	3.2
MLP-170	MLP-170	9.7	3.4
MLP-200	MLP-200	10.4	3.4
MLP-230	MLP-230	10.9	3.6
MLP-260	MLP-260	11.5	3.8
MLP-290	MLP-290	11.8	3.9
MLP-320	MLP-320	12.3	4.1
MLP-350	MLP-350	12.8	4.3
MLP-380	MLP-380	13.2	4.4
MLP-435	MLP-435	13.4	4.5
MLP-470	MLP-470	13.9	4.5
MLP-505	MLP-505	14.2	4.7

## MHP - High Profile (12 sizes)

Catalogue Number	Product Size (g)	Diameter A (cm)	Projection B (cm)
MHP-100	100	8.7	2.3
MHP-130	130	9.0	3.0
MHP-160	160	9.4	3.5
MHP-190	190	9.5	4.0
MHP-230	230	10.0	4.3
MHP-260	260	10.5	4.6
MHP-300	300	11.0	4.8
MHP-340	340	11.5	5.0
MHP-380	380	11.7	5.3
MHP-410	410	12.0	5.4
MHP-460	460	12.3	5.8
MHP-525	525	12.7	6.2

**CML/CMH**  
**Cohesive Gel**  
**Textured Surface**




## CML - Low Profile (17 sizes)

Catalogue Number	Product Size (g)	Diameter A (cm)	Projection B (cm)
CML-080	080	7.6	2.6
CML-110	110	8.6	2.8
CML-140	140	8.9	3.3
CML-170	170	9.8	3.3
CML-200	200	10.7	3.4
CML-230	230	11.2	3.5
CML-265	265	11.7	3.7
CML-295	295	11.9	3.9
CML-335	335	12.4	4.1
CML-360	360	12.7	4.2
CML-390	390	12.9	4.4
CML-435	435	13.4	4.5
CML-470	470	13.9	4.5
CML-505	505	14.2	4.7
CML-620	620	15.5	4.8
CML-710	710	16.2	5.0
CML-800	800	16.9	5.1

## CMH - High Profile (9 sizes)

Catalogue Number	Product Size (g)	Diameter A (cm)	Projection B (cm)
CMH-160	160	9.1	3.8
CMH-190	190	9.3	4.2
CMH-230	230	9.9	4.6
CMH-280	280	10.4	5.0
CMH-310	310	10.7	5.2
CMH-365	365	11.4	5.4
CMH-410	410	11.8	5.7
CMH-460	460	12.3	5.8
CMH-525	525	12.7	6.2

**SLD/SHD**  
**Responsive Gel**  
**Smooth Surface**



## SLD - Low Profile (17 sizes)

Catalogue Number	Product Size (g)	Diameter A (cm)	Projection B (cm)
SLD-110	110	8.6	2.6
SLD-140	140	8.7	3.1
SLD-170	170	9.5	3.4
SLD-200	200	10.2	3.4
SLD-230	230	10.7	3.4
SLD-260	260	11.0	3.5
SLD-290	290	11.7	3.5
SLD-320	320	12.3	3.5
SLD-350	350	12.5	3.8
SLD-380	380	13.1	3.8
SLD-410	410	13.4	3.8
SLD-440	440	13.8	3.9
SLD-470	470	14.1	3.9
SLD-500	500	14.4	3.9
SLD-620	620	15.5	4.8
SLD-710	710	16.2	5.0
SLD-800	800	16.9	5.1

## SHD - High Profile (13 sizes)

Catalogue Number	Product Size (g)	Diameter A (cm)	Projection B (cm)
SHD-100	100	8.8	2.2
SHD-130	130	9.0	2.9
SHD-160	S160	9.1	3.7
SHD-190	190	9.4	3.7
SHD-230	230	9.9	4.0
SHD-260	260	10.6	4.0
SHD-300	300	10.9	4.3
SHD-340	340	11.3	4.3
SHD-380	380	11.7	4.7
SHD-410	410	11.9	4.7
SHD-440	440	12.4	5.0
SHD-470	470	12.7	5.0
SHD-500	500	12.7	5.3

Nominal dimensions: device dimensions are measured with the device placed on a flat surface. Not every device will conform to the dimensions given, slight variations may occur.

Nominal dimensions: device dimensions are measured with the device placed on a flat surface. Not every device will conform to the dimensions given, slight variations may occur.

Nominal dimensions: device dimensions are measured with the device placed on a flat surface. Not every device will conform to the dimensions given, slight variations may occur.